


Refrigeration Controls



INSTRUCTIONS

AKS 11
Pt 1000 ohm

084R9690



| ohm | °C | °F |
|-----|-----|-----|
| 803 | -50 | -58 |
| 807 | -49 | -56 |
| 811 | -48 | -54 |
| 815 | -47 | -53 |
| 819 | -46 | -51 |
| 823 | -45 | -49 |
| 827 | -44 | -47 |
| 831 | -43 | -45 |
| 835 | -42 | -44 |
| 839 | -41 | -42 |
| 843 | -40 | -40 |
| 847 | -39 | -38 |
| 851 | -38 | -36 |
| 855 | -37 | -35 |
| 859 | -36 | -33 |
| 862 | -35 | -31 |
| 866 | -34 | -29 |
| 870 | -33 | -27 |
| 874 | -32 | -26 |
| 878 | -31 | -24 |
| 882 | -30 | -22 |
| 886 | -29 | -20 |
| 890 | -28 | -18 |
| 894 | -27 | -17 |
| 898 | -26 | -15 |
| 902 | -25 | -13 |
| 906 | -24 | -11 |
| 910 | -23 | -9 |
| 914 | -22 | -8 |

| ohm | °C | °F |
|------|-----|----|
| 918 | -21 | -6 |
| 922 | -20 | -4 |
| 926 | -19 | -2 |
| 929 | -18 | 0 |
| 933 | -17 | 1 |
| 937 | -16 | 3 |
| 941 | -15 | 5 |
| 945 | -14 | 7 |
| 949 | -13 | 9 |
| 953 | -12 | 10 |
| 957 | -11 | 12 |
| 961 | -10 | 14 |
| 965 | -9 | 16 |
| 969 | -8 | 18 |
| 973 | -7 | 19 |
| 977 | -6 | 21 |
| 980 | -5 | 23 |
| 984 | -4 | 25 |
| 988 | -3 | 27 |
| 992 | -2 | 28 |
| 996 | -1 | 30 |
| 1000 | 0 | 32 |
| 1004 | 1 | 34 |
| 1008 | 2 | 36 |
| 1012 | 3 | 37 |
| 1016 | 4 | 39 |
| 1020 | 5 | 41 |
| 1023 | 6 | 43 |
| 1027 | 7 | 45 |

| ohm | °C | °F |
|------|----|----|
| 1031 | 8 | 46 |
| 1035 | 9 | 48 |
| 1039 | 10 | 50 |
| 1043 | 11 | 52 |
| 1047 | 12 | 54 |
| 1051 | 13 | 55 |
| 1055 | 14 | 57 |
| 1058 | 15 | 59 |
| 1062 | 16 | 61 |
| 1066 | 17 | 63 |
| 1070 | 18 | 64 |
| 1074 | 19 | 66 |
| 1078 | 20 | 68 |
| 1082 | 21 | 70 |
| 1086 | 22 | 72 |
| 1090 | 23 | 73 |
| 1093 | 24 | 75 |
| 1097 | 25 | 77 |
| 1101 | 26 | 79 |
| 1105 | 27 | 81 |
| 1109 | 28 | 82 |
| 1113 | 29 | 84 |
| 1117 | 30 | 86 |
| 1121 | 31 | 88 |
| 1124 | 32 | 90 |
| 1128 | 33 | 91 |
| 1132 | 34 | 93 |
| 1136 | 35 | 95 |

Approx. 4 ohm/°C Approx. 2.25 ohm/°F

